






		Conditions	
cell type:		NiMH	
cell size:		AAA	
nominal voltage:	1.2	V	
max. charge voltage:	1.5	V	at standard charge (0.1C / 20°C)
capacity			
nominal:	800	mAh	discharge at 0.2C
minimum:	750	mAh	discharge at 0.2C
	700	mAh	discharge at 1C
			1.0V end discharge voltage
			ta: 20°C
max. continuous discharge current:	1600	mA	ta: 0...45°C
charge			
standard charge:	80	mA	14....16hrs
quick charge:	240	mA	4hrs
fast charge:	800	mA	1.1hrs
recommended charge termination control parameters:	0...5	mV	-ΔV (-delta V)
	0.8...1	°C	temperature rise per minute
	45...50	°C	TCO (temperature cut off)
trickle charge current:	5...20	mA	(recommended)
continuous overcharge: (less than 1 year)	≤ 80	mA	no conspicuous deformation no leakage
internal resistance: (impedance)	≤ 40	mΩ	at 1KHz battery fully charged
life expectancy:	≥ 1500	cycles	acc. IEC standard
self discharge			
charge retention:	≥ 85	%	after 12 months storage at 20°C
initial capacity:	≥ 550	mAh	within 30 days after delivery discharge at 0.2C
ambient temperature range:			
	0...45	°C	standard charge
	0...40	°C	fast charge
	0...50	°C	discharge
	- 20...50	°C	storage (≤3months)
	- 20...40	°C	storage (≤6months)
	- 20...30	°C	storage (≤24months)

QCT1: 20/725/45
QCT2: 30/675/45

mechanical specifications			
cell dimensions			
diameter d1:		10.5 - 0.7	mm
diameter d2:	max.	3.8	mm
height h1:		44.5 - 1.5	mm
height h2:	min.	0.8	mm
weight:		13 ± 2	g



Diagrams



	ANSMANN Specifications for model:	NiMH Battery
		AAA - 800mAh low self discharge
	data sheet no. / part no.	
	supplier no.	703642
	author / date	TG / 01.08.2018