

Overview

The LA12 Magnetic Direct Current Sensors (MDCS™) use our proprietary magnetic material and hall element for magnetic detection of both direct current (DC) and alternating current (AC) as well as pulse current. The output voltage varies in proportion to the strength of the current measured.

Applications

Typical applications include inverter-based home appliances (air conditioners), general purpose inverters, AC variable-speed drives and servo drives, industrial machinery, UPSs, and DC motor controls.

Benefits

- Detection of DC, AC and pulse currents
- Limited fluctuations in output from changes in the power supply voltage and the ambient temperature
- Excellent linearity of the measured current and the converted power output
- Measured current and secondary output side are insulated
- Compact and lightweight
- RoHS compliant




Ordering Information

LA12-	10	V21
Series	Rated Current AC (A)	Output Voltage (V)
LA12	10 48 50 60	V21 = 2

Dimensions in mm


LA12-10V21



Pin Number	LA12
1	NC
2	GND (Ground pin)
3	Vcc (+12 V)
4	V _{out} (Output voltage pin)
A	(Measured current ⊕ pin)
B	(Measured current Φ pin)

Dimensions in mm (cont.)


LA12-48V21, LA12-50V21, & LA12-60V21



Pin Number	LA12
1	NC
2	GND (Ground pin)
3	Vcc (+12 V)
4	V _{out} (Output voltage pin)
A	(Measured current ⊕ pin)
B	(Measured current Φ pin)

AC Output Characteristics

Output Voltage Example LA12-10V21



Environmental Compliance

All MDCS sensors are RoHS compliant.

Specifications

Item	Performance Characteristics
Rated Current	10 – 60 A
Power Supply Voltage	12 V
Consumption Current	40 mA Maximum
Output Voltage	2,000 \pm 0.06 V
Residual Voltage	2,500 \pm 0.06 V
Hysteresis	60 mV Maximum
Pulse Response	20 μ s maximum (di/dt = 100 AT/ μ s)
Linearity	-2 to 2
Insulation Withstand Voltage	2,000 VAC/1 minute
Insulation Resistance	500 VDC to 500 M Ω
Operating Temperature Range	-10°C to +75°C
Storage Temperature Range	-15°C to +80°C

Table 1 – Ratings & Part Number Reference

Part Number	Rated Current (A)	Primary Side Windings (Turn)	Scope of Measurement	Power Supply Voltage ¹ (V)	Output Voltage ² (V)	Residual Voltage ³ (V)	Insulation Withstand Voltage ⁴	Insulation Resistance ⁴	Weight (g)
LA12-10V21	10	6	0 to 100% of rated current	12 ±5%	2,000 ±0.06	2,500 ±0.06	2,000 VAC /1 minute	500 VDC to 500 MΩ	9.0
LA12-48V21	48	2							7.8
LA12-50V21	50	2							7.8
LA12-60V21	60	1							7.4

¹ A power supply voltage variation 30 mV maximum

² At rated current and $R_L = 10\text{ k}\Omega$, temperature characteristics $\pm 0.15\% / ^\circ\text{C}$

³ At 0A and $R_L = 10\text{ k}\Omega$, temperature characteristics $\pm 4\text{ mV} / ^\circ\text{C}$

⁴ Between wire and terminals

Soldering Process

LA12-10V21, LA12-48V21, LA12-50V21 & LA12-60V21

Reflow Soldering	Heating temperature	260°C
	Heating time	within 10 seconds
Iron Soldering	Temperature of tip	350°C or lower
	Worktime	within 3 seconds

Packaging

Part Number	Packaging Type	Pieces per Box
LA12-10V21	Tray	400
LA12-48V21		
LA12-50V21		
LA12-60V21		

Handling Precautions

Precautions for product storage

Current Sensors should be stored in normal working environments. While the sensors are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long-term storage.

KEMET recommends that maximum storage temperature not exceed 80°C and atmospheres should be free of chlorine and sulfur-bearing compounds. Temperature fluctuations should be minimized to avoid condensation on the parts. Also, avoid storage near strong magnetic fields as this might magnetize the product and could cause its characteristics to change. Limit ambient magnetic fields to 50e or less.

For optimized solderability, Current Sensor's stock should be used preferably within 12 months of receipt.

Before using magnetic direct current sensors

- Do NOT drop or apply any other mechanical stress as it may change the performance characteristics.
- Do NOT exceed 260°C for 10 seconds when soldering, this is the maximum heat resistance grade of these sensors. Use a low-corrosion type flux when soldering.
- Do NOT apply strong static electricity, as the circuit uses ICs, this could cause damage. Take static electricity precautions when handling.

Export Control

For customers in Japan

For products that are controlled items subject to the "Foreign Exchange and Foreign Trade Law" of Japan, the export license specified by the law is required for export.

For customers outside Japan

Sensors should not be used or sold for use in the development, production, stockpiling or utilization of any conventional weapons or mass-destructive weapons (nuclear weapons, chemical or biological weapons, or missiles), or any other weapons.

KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as the installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

KEMET is a registered trademark of KEMET Electronics Corporation.