

## Specification Sheet

Part Number: 156-00864



**Article Number**

156-00864

**Type**

T50ROSEC5A

**Color**

Black (BK)

**Features & Benefits**

- Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.
- Edge Clip provides low insertion force and high extraction force ideal for assembly environments.
- Two piece assembly allows the mount to slide along the strap ensuring proper orientation.
- Cable tie is outside serrated to reduce bundle chafing.

**Quantity Per**

bag

**Product Description**

HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

**Short Description**

Outside Serrated Cable Tie &amp; Edge Clip, 8.0" Long, EC5A, 1–3 mm Panel, 50lb, PA66HS, Black, 500/pkg

**Global Part Name**

T50ROSEC5A-PA66HS/PA66HIRHS-BK

**Minimum Tensile Strength (Imperial)**

50.0

**Minimum Tensile Strength (Metric)**

225

**Length L (Imperial)**

8.0

**Length L (Metric)**

202.0

**Fixation Method**

EdgeClip, sideways, assembled, 2 piece

**Identification Plate Position**

none

**Releasable Closure**

No

**Variant**

Outside Serrated

**Width W (Imperial)**

0.18

**Width W (Metric)**

4.6

**Bundle Diameter Min (Imperial)**

0.20

**Bundle Diameter Min (Metric)**

5.0

**Bundle Diameter Max (Imperial)**

2.0

**Bundle Diameter Max (Metric)**

50.0

<b>Thickness T (Imperial)</b>	0.05
<b>Thickness T (Metric)</b>	1.2
<b>Height H (Imperial)</b>	.05
<b>Height H (Metric)</b>	1.30
<b>Panel Thickness Min(Imperial)</b>	0.04
<b>Panel Thickness Max(Imperial)</b>	0.12
<b>Panel Thickness Min (Metric)</b>	1.0
<b>Panel Thickness Max (Metric)</b>	3.0
<b>Material</b>	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
<b>Material Shortcut</b>	PA66HS PA66HIRHS
<b>Material Cable Tie</b>	Polyamide 6.6 heat stabilized (PA66HS)
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +221°F (-40°C to +105°C) -40°F to +230°F (-40°C to +110°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	500

**Package Quantity (Metric)**

500

**Customs Number**

3926909987

**Weight (Metric)**

4.5