

Specification Sheet

Part Number: 156-00551



Cable Tie & Edge Clip, 8.0" Long, EC9, 1–3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg

Article Number	156-00551
Type	T50REC9SD
Color	Black (BK)
Features & Benefits	• Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole. • Edge Clip provides low insertion force and high extraction force ideal for assembly environments.
Quantity Per	bag

Product Description

The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

Short Description	Cable Tie & Edge Clip, 8.0" Long, EC9, 1–3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg
Global Part Name	T50REC9SD-PA66HS/PA66HIRHS-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.0
Length L (Metric)	202.0
Fixation Method	EdgeClip, top, assembled, 2 piece
Identification Plate Position	none
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.20
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	2.0
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.05

Thickness T (Metric)	1.2
Height H (Imperial)	0.047
Height H (Metric)	1.2
Panel Thickness Min(Imperial)	0.04
Panel Thickness Max(Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C) -40°F to +230°F (-40°C to +110°C)
Minimum Extraction Force (Imperial)	50.0
Minimum Extraction Force (Metric)	225
ROHS Complaint	Yes

Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909987