

Productname : F2 SPÉCIAL CONTACTS
 Ref.Nr.: BDS002206_3_20171006 (EN)

Creationdate : 06.10.17 Version : 1.0
 Replaces:

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

F2 SPÉCIAL CONTACTS
 Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Precision

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe bvba
 Touwslagerstraat 1
 9240 Zele
 Belgium
 Tel.: +32(0)52/45.60.11
 Fax.: +32(0)52/45.00.34
 E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Laurinkatu 57 A 23 B, 08100 Lohja	+358/(19)32.921	
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Laxfiskevägen 16, 433 38 Partille	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Aerosols, category 1
 Extremely flammable aerosol.
 Pressurised container: May burst if heated.

Classification is based on test data.



Productname : F2 SPÉCIAL CONTACTS
Ref.Nr.: BDS002206_3_20171006 (EN)
Creationdate : 06.10.17 Version : 1.0
Replaces:

Health: Skin irritation, category 2
 Causes skin irritation.
 Specific target organ toxicity - single exposure, category 3
 May cause drowsiness or dizziness.

Classification based on calculation method.

Environment: Hazardous to the aquatic environment, chronic category 2
 Toxic to aquatic life with long lasting effects.

Classification based on calculation method.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier: Contains:
 hydrocarbons

Hazard pictogram(s):



Signal word: Danger

Hazard statement(s): H222 : Extremely flammable aerosol.
 H229 : Pressurised container: May burst if heated.
 H315 : Causes skin irritation.
 H336 : May cause drowsiness or dizziness.
 H411 : Toxic to aquatic life with long lasting effects.

Precautionary statement(s): P102 : Keep out of reach of children.
 P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 P211 : Do not spray on an open flame or other ignition source.
 P251 : Do not pierce or burn, even after use.
 P261 : Avoid breathing dust/fume/gas/mist/vapours/spray.
 P271 : Use only outdoors or in a well-ventilated area.
 P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
 P501-2 : Dispose of contents/container to an authorised waste collection point.

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
----------------------	---------------------	---------	-------	-------	---------------------------	------------------	-------



Productname : F2 SPÉCIAL CONTACTS
Ref.Nr.: BDS002206_3_20171006 (EN)

Creationdate : 06.10.17 Version : 1.0
Replaces:

pentane	01-2119459286-30	109-66-0	203-692-4	25-50	Flam. Liq. 2, Asp. Tox. 1, STOT SE 3, Aquatic Chronic 2	H225,H304,H336,H411	A
hydrocarbons,C6,isoalkanes,< 5% n-hexane	01-2119484651-34	-	(931-254-9)	25-50	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H225,H315,H336,H304,H411	Q
Hydrocarbons, C6-C7, isoalkanes, cyclics, < 5% n-hexane	01-2119486291-36	-	(926-605-8)	5-10	Flam. Liq. 2, Asp. Tox. 1, STOT SE 3, Aquatic Chronic 2	H225,H304,H336,H411	B,Q
carbon dioxide	-	124-38-9	204-696-9	1-5	Press. Gas	H280	A,G
Hydrocarbons, C13-15, n-alkanes, isoalkanes, cyclics, < 2% aromatics	01-2119453414-43	-	(920-107-4)	1-5	Asp. Tox. 1	H304	B,Q
white mineral oil (petroleum)	01-2119487078-27	8042-47-5	232-455-8	<1	Asp. Tox. 1	H304	B
cyclohexanol	01-2119447488-26	108-93-0	203-630-6	<0.1	Acute Tox. 4, Acute Tox. 4, STOT SE 3, Skin Irrit. 2	H332,H302,H335,H315	B
cyclohexanone	01-2119453616-35	108-94-1	203-631-1	<0.001	Flam. Liq. 3, Acute Tox. 4	H226,H332	A

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)of REACH Regulation No 1907/2006

Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures**4.1. Description of first aid measures**

Contact with eyes :	IF IN EYES: Rinse cautiously with water for several minutes. If eye irritation persists: Get medical advice/attention.
Contact with skin :	Take off contaminated clothing and wash before reuse. IF ON SKIN: Rinse cautiously with water for several minutes. If skin irritation occurs: Get medical advice/attention.
Inhalation :	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Ingestion :	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.



Productname : F2 SPÉCIAL CONTACTS
Ref.Nr.: BDS002206_3_20171006 (EN)

Creationdate : 06.10.17 Version : 1.0
Replaces:

Skin contact :	Symptoms : sore throat, abdominal pain, nausea, vomiting Irritating to skin
Eye contact :	Symptoms : redness and pain May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice : If you feel unwell, seek medical advice (show the label where possible)
If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2
HF may be formed under condition of fire

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8



Productname : F2 SPÉCIAL CONTACTS
Ref.Nr.: BDS002206_3_20171006 (EN)

Creationdate : 06.10.17 Version : 1.0
Replaces:

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
 Take precautionary measures against static discharges
 Equipment should be earthed
 Use explosion-proof electrical/ventilating/lighting/.../equipment.
 Use only non-sparking tools.
 Do not breathe aerosols or vapours.
 Ensure adequate ventilation
 Avoid contact with skin and eyes.
 Wash thoroughly after use
 Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
 Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Precision

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
cyclohexanone	108-94-1	TWA	10 ppm
		STEL	20 ppm
pentane	109-66-0	TWA	1000 ppm
carbon dioxide	124-38-9	TWA	9000 mg/m3
		STEL	1800 mg/m3

8.2. Exposure controls

Control procedures : Ensure adequate ventilation
 Keep away from heat and sources of ignition
 Take precautionary measures against static discharges

Personal protection : Take precautions to avoid contact with skin and eyes when handling the product.
 In all cases handle and use the product in accordance with good industrial hygiene practices.
 Ensure adequate ventilation



Productname : F2 SPÉCIAL CONTACTS
Ref.Nr.: BDS002206_3_20171006 (EN)

Creationdate : 06.10.17 Version : 1.0
Replaces:

inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type AX)
hands and skin :	When handling the product wear chemical-resistant gloves (standard EN 374). Use a reusable glove with a minimum breakthrough time of 30 minutes. The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	Nitrile
eyes :	Wear safety eyewear according to EN 166.
Environmental protection:	Avoid release to the environment. Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Apperance : physical state :	Liquid under pressure.
colour :	Colorless.
odour :	Solvent.
pH :	Not applicable.
Boiling point/range :	Not available.
Flash point :	< 0 °C (Closed Cup)
Evaporation rate :	Not available.
Explosion limits : upper limit :	Not available.
lower limit :	Not available.
Vapour pressure :	Not available.
Relative density :	0.67 g/cm ³ (@ 20°C).
Solubility in water :	Insoluble in water
Auto-ignition :	> 200 °C
Viscosity :	Not applicable.

9.2. Other information

VOC = volatile organic compounds	700 g/l
---	---------

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose



Productname : F2 SPÉCIAL CONTACTS
Ref.Nr.: BDS002206_3_20171006 (EN)

Creationdate : 06.10.17 Version : 1.0
Replaces:

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2
 HF may be formed under condition of fire

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	Causes skin irritation.
serious eye damage/irritation:	based on available data the classification criteria are not met
respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	May cause drowsiness or dizziness.
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Irritating to skin
Eye contact :	May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
pentane	109-66-0	LD50 oral rat	> 5000 mg/kg
		LD50 derm.rabit	> 3000 mg/kg
white mineral oil (petroleum)	8042-47-5	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 5 mg/l
		LD50 derm.rabit	> 2000 mg/kg
Hydrocarbons, C13-15, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	LD50 oral rat	> 5000 mg/kg



Productname : F2 SPÉCIAL CONTACTS
Ref.Nr.: BDS002206_3_20171006 (EN)

Creationdate : 06.10.17 Version : 1.0
Replaces:

		LC50 inhal.rat	> 4951 mg/l
		LD50 derm.rabit	> 5000 mg/kg
Hydrocarbons, C6-C7, isoalkanes, cyclics, < 5% n-hexane	-	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 2000 mg/kg
hydrocarbons,C6,isoalkanes,< 5% n-hexane	-	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 3000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 2
 Toxic to aquatic life with long lasting effects.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
Hydrocarbons, C13-15, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	IC50 algae	1000 mg/l
		LC50 fish	1000 mg/l
		EC50 daphnia	1000 mg/l
Hydrocarbons, C6-C7, isoalkanes, cyclics, < 5% n-hexane	-	IC50 algae	55 mg/l
		LC50 fish	12 mg/l
		EC50 daphnia	3 mg/l
hydrocarbons,C6,isoalkanes,< 5% n-hexane	-	IC50 algae	55 mg/l
		LC50 fish	> 1 mg/l
		EC50 daphnia	3.87 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects



Productname : F2 SPÉCIAL CONTACTS
Ref.Nr.: BDS002206_3_20171006 (EN)

Creationdate : 06.10.17 Version : 1.0
Replaces:

No experimental data available

GWP (global warming potential): 2

(calculated in accordance with Annex IV of Regulation (EU) No 517/2014 on fluorinated greenhouse gases)

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.

Contaminated packaging : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS (naphta, pentane)

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: Yes
IMDG - Marine pollutant: Marine pollutant
IATA/ICAO - Environmentally hazardous: Yes

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203



Productname : F2 SPÉCIAL CONTACTS
Ref.Nr.: BDS002206_3_20171006 (EN)

Creationdate : 06.10.17 Version : 1.0
Replaces:

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Regulation (EC) No 1907/2006 (REACH)
Regulation (EC) No 1272/2008 (CLP)
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: H225 : Highly flammable liquid and vapour.
H226 : Flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H302 : Harmful if swallowed.
H304 : May be fatal if swallowed and enters airways.
H315 : Causes skin irritation.
H332 : Harmful if inhaled.
H335 : May cause respiratory irritation.
H336 : May cause drowsiness or dizziness.
H411 : Toxic to aquatic life with long lasting effects.

acronyms and synonyms: TWA = time weight average
STEL = short time exposure limit
VOC = volatile organic compounds
PBT = persistent bioaccumulative toxic
vPvB = very persistent very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

