

Sound Level Meter



**RoHS
Compliant**



Specifications

Standard Applied	: IEC651 type 2, ANSI S1.4 type 2
Frequency Range	: 31.5Hz to 8kHz
Measuring Level Range	: 30 to 130dB
Resolution	: 0.1dB
Accuracy	: ± 1.4dB (under reference conditions)
Frequency Weighting	: A & C
Time Weighting	: Fast: 125ms; Slow: 1s
Level Ranges	: Low: 30 ~ 100dB; High: 60 ~ 130dB
Display	: 4-Digit LCD
Display Update	: 0.5s
Alarm Function	: "OVER" is shown when input is out of range
Maximum Hold	: Hold readings the Maximum Value, with decay < 1dB / 3minutes
Microphone	: ½ inch electret condenser microphone
Calibration	: Electrical calibration with the internal oscillator (1kHz Sine Wave)
Auto Power Off	: Meter automatically shuts down after approx. 15minutes of inactivity
Operating Temperature	: 0°C to 40°C (32°F to 104°F)
Operating Humidity	: 10 to 90% RH
Storage Temperature	: -10°C to 60°C (14°F to 140°F)
Storage Humidity	: 10 to 75% RH
Power Supply	: One 9V Battery, 006P or IEC 6F22 or NEDA 1604 (Included)
Battery Life	: About 50hrs (Alkaline Battery)
Dimensions	: 210mm x 55mm x 32mm (8.26" x 2.16" x 1.25")
Weight	: 230g (8.11oz) (Including Battery)
Includes	: 9V Battery, Carrying Case, Instruction Manual

Part Number Table

Description	Part Number
Sound Level Meter, 30dB to 130dB, ±1.4dB	72-942

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

