


W0998

37mm/1 1/2" Swivel Castor.

Part Number	Description
W0998	




FIXING HOLES 7mm/.27"DIA

W0958

50mm / 2" Push in Castor with Metal Socket included.
Carrying Weight per wheel 20kg/44lb

Material: Steel

Part Number	Description
W0958	




5295 - 5299

50mm/2" Plug-In Castor, with Soft Rubber Black Wheel.
Mates with Socket Part 5299.
Load Capacity 45.359Kg/100Lb
Special Order outside USA & China

Material: Steel

Part Number	Finish	Description
5295	Zinc	
5295N	Nickel	
5299	Zinc	Socket




W0997TP

50mm/2" Castor Wheel.

Material: Thermo Plastic/Rubber

Part Number	Description
W0997TP	




FIXING SLOTS 8 x 6mm
.30" x .24"

W0960

50mm/2" Swivel Castor.
Grey Wheel with Roller Bearings.
Carrying Weight per wheel 40kg/88lb

Material: Pressed Steel

Part Number	Finish	Description
W0960	Zinc	



FIXING SLOTS 8mmx6mm/D.314x0.236"

W0995

50mm/2" **Braked** Swivel Castor.
Grey Wheel with Roller Bearings.
Carrying Weight per wheel 40kg/88lb

Material: Pressed Steel

Part Number	Finish	Description
W0995	Zinc	