



Belden Style LSF Multi-pair Unscreened Cable

Product Type:
Belden Style Cable

Application:
General purpose audio, instrumentation and control applications.

Standards / Conformances:
REACH & RoHS Compliant

Construction:

Conductor:	Stranded tinned annealed copper, as per table below.
Insulation:	PVC
Core:	Pairs cabled together
Screen:	An overall aluminised polyester tape with tinned copper drain wire applied in contact with the tape screen
Sheath:	LSF (flame retardant PVC)

Physical Characteristics:

Our Part Number	Equivalent Belden Type	No. of Pairs	Conductor (AWG)	Insulation	Core Colour	Sheath Colour	Overall Diameter (mm)
B0217A***	8442	1	22	PVC	Black/Red	Grey	4.3
B0033AB***	8471	1	16	PVC	Black/White	Grey	6.9
B0219A***	9156	2	18	PVC	1 Black/Red 2 Black/White	Grey	8.4

Note: *** refers to the length, in metres.



Suppliers of Quality Assured Cables

Electrical Characteristics:

Our Part Number	Nominal Conductor Resistance @ 20°C (Ω/km)	Nominal Capacitance Core to Core (pF/m)	Voltage Rating
B0217A	51.2	30	300V
B0033AB	14.7	108.2	300V
B0219A	19.2	25.5	300V

Environmental Characteristics:

Rated Temperature : 60 °C