
























Features

- 5"×3" compact size
- Medical safety approved (2 x MOPP) accroding to ANSI/AAMI ES60601-1 and IEC/EN60601-1
- Suitable for BF application with appropriate system configuration
- · 250W convection,400W force air
- EMI Class B for Class I & Class A for Class II configuration
- No load power consumption<0.5W by PS-ON control
- 5Vdc standby output, 12Vdc fan supply, Power Good, Power Fail and remote sense
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Operating altitude up to 4000 meters
- 3 years warranty

Description

RPS-400 is a 400W highly reliable green PCB type medical power supply with a high power density on the 5" by 3" footprint. It accepts $80\sim264$ VAC input and offers various output voltages between 12V and 48V. The working efficiency is up to 94% and the extremely low no load power consumption is down below 0.5W. RPS-400 is able to be used for both Class I (with FG) or Class II (no FG) system design. The extremely low leakage current is less than $160~\mu$ A. In addition, it conforms to international medical regulations (2*MOPP) and EMC EN55011, perfectly fitting all kinds of BF rated "patient contact" medical system equipment. RPS-400 series also offers the enclosed style models(-C/TF/SF)

Model Encoding



Туре	Description	Note
Blank	PCB Type	In stock
С	Enclosed casing Type	In stock
TF	Enclosed Type with fan on the top	In stock
SF	Enclosed Type with fan on the side	In stock

Applications

- Oral irrigator
- · Hemodialysis machine
- Medical computer monitors
- · Sleep apnea devices
- · Pump machine
- · Electric bed



SPECIFICATION

MODEL			RPS-400-12	RPS-400-15	RPS-400-18	RPS-400-24	RPS-400-27	RPS-400-36	RPS-400-48
	DC VOLTAGE		12V	15V	18V	24V	27V	36V	48V
	OUDDENT	25CFM	33.3A	26.7A	22.3A	16.7A	14.9A	11.2A	8.4A
	CURRENT	Convection	20.8A	16.7A	13.9A	10.5A	9.3A	7A	5.3A
	RATED	25CFM	399.6W	400.5W	401.4W	400.8W	402.3W	403.2W	403.2W
	POWER	Convection	249.6W	250.5W	250.2W	252W	251.1W	252W	254.4W
	RIPPLE & NOIS	SE (max.) Note.2	120mVp-p	120mVp-p	150mVp-p	150mVp-p	200mVp-p	200mVp-p	200mVp-p
OUTPUT	VOLTAGE ADJ. RA	NGE(main output)	11.4~12.6V	14.3~15.8V	17.1~18.9V	22.8~25.2V	25.6 ~ 28.4V	34.2~37.8V	45.6 ~50.4V
	VOLTAGE TOL	ERANCE Note.3	±3.0%	±3.0%	±3.0%	±2.0%	±1.0%	±1.0%	±1.0%
	LINE REGUL	ATION	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%
	LOAD REGU	LATION	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%
	SETUP, RISE	TIME	1000ms, 30ms/	230VAC 15	00ms, 30ms/115	VAC at full load	"	1	
	HOLD UP TIM	ІЕ (Тур.)	16ms/230VAC	16ms/115VAC	at full load				
	VOLTAGE RA	NGE Note.4	80 ~ 264VAC	113 ~ 370VD	С				
	FREQUENCY	RANGE	47 ~ 63Hz						
	POWER FACTOR		PF>0.94/230VAC PF>0.98/115VAC at full load						
INPUT	EFFICIENCY (Typ.)		91.5%	92%	93%	93%	93.5%	94%	94%
	AC CURRENT (Typ.)		4.2A/115VAC 2.1A/230VAC						
	INRUSH CUR	RENT (Typ.)	COLD START 35A/115VAC 70A/230VAC						
	LEAKAGE CURRENT (max.) Note.5		Earth leakage current < 200 µA/264 VAC 50 Hz , Touch current < 70 µA/264 VAC						
	OVERLOAD		105 ~ 135% rated output power						
	OVERLOAD		Protection type: Hiccup mode, recovers automatically after fault condition is removed						
PROTECTION	OVER VOLTAGE		13.2 ~ 15.6V	16.5 ~ 19.5V	19.8 ~23.4V	26.4 ~ 31.2V	29.7 ~ 35.1V	39.6 ~ 46.8V	52.8 ~ 62.4V
			Protection type	: Shut down o/p	voltage, re-powe	r on to recover	•		
	OVER TEMPERATURE		Protection type : Shut down o/p voltage, recovers automatically after temperature goes down						
	5V STANDBY	,	5Vsb:5V@0.6A without fan, 1A with fan 25CFM; Tolerance ±2%, ripple:120mVp-p(max.)						
	FAN SUPPLY		12V@0.5A for driving fan ; Tolerance ±10%						
FUNCTION	PS-ON INPUT	T SIGNAL	Power on: PS-ON = "Hi" or " > 2 ~ 5V"; Power off: PS-ON = "Low" or " < 0 ~ 0.5V"						
	POWER GOOD	/ POWER FAIL	500ms>PG>10ms; The TTL signal goes high with 10ms to 500ms delay after power set up; The TTL signal goes low at least 1ms before Vo below 90% of rated value						
	WORKING TE	EMP.	-30 ~ +70°C (Refer to "Derating Curve")						
	WORKING H	UMIDITY	20 ~ 90% RH non-condensing						
ENVIRONMENT	STORAGE TEI	MP., HUMIDITY	-40 ~ +85°C, 10) ~ 95% RH non-	condensing				
	TEMP. COEF	FICIENT	±0.03%/°C (0	~ 50°C)					
	VIBRATION		10 ~ 500Hz, 20	3 10min./1cycle,	60min, each ald	ong X, Y, Z axes			
	OPERATING A	LTITUDE Note.6	4000 meters						



SPECIFICATION

	SAFETY STANDARDS	IEC60601-1, TUV EN60601-1, EAC TP TC 004, UL ANSI / AAMI ES60601-1 (3.1 version), CAN/CSA-C22.2 No. 60601-1:14 - Edition 3 approved;							
		Design refer to E		dition	3 approved;				
	ISOLATION LEVEL	Primary-Secondary:	2xMOPP, Prim	nary-Ea	rth:1xMOPP, Seconda	ary-Ear	th:1xMOPP		
	WITHSTAND VOLTAGE	I/P-O/P:4KVAC I/P	-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.5KVAC						
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG:100	P-O/P, I/P-FG:100M Ohms / 500VDC / 25°C / 70% RH						
		Parameter		Stand	ard		Test Level / N	lote	
		Conducted emission		EN550	11 (CISPR11)		Class B(Pleas	se see last page note1)	
	EMC EMISSION	Radiated emission		EN550	11 (CISPR11)		Class B(Pleas	se see last page note1)	
SAFETY &		Harmonic current		EN610	000-3-2		Class A		
EMC		Voltage flicker		EN610	EN61000-3-3				
(Note 7)		EN55024 , EN60601-1-2, EN61204-3							
		Parameter		Standard			Test Level / Note		
		ESD		EN610	000-4-2		Level 4, 15KV a	ir; Level 4, 8KV contact	
		RF field susceptibility		EN61000-4-3			,	80MHz~2.7GHz) n(385MHz~5.78GHz)	
	EMC IMMUNITY	EFT bursts		EN610	000-4-4		Level 3, 2KV		
		Surge susceptibility		EN610	000-4-5		Level 4, 4KV/Li	ne-FG ; 2KV/Line-Line	
		Conducted susceptibility		EN61000-4-6			Level 3, 10V		
		Magnetic field immunity		EN61000-4-8			Level 4, 30A/r	m	
		Voltage dip, interruption		EN61000-4-11			100% dip 1 periods, 30% dip 25 periods, 100% interruptions 250 periods		
	MTBF	194.1Khrs min. M	L-HDBK-217F						
	DIMENSION	Туре	RPS-400		RPS-400-C	RPS-	400-TF	RPS-400-SF	
	DIMENSION	1 +10/41 1	127*76.2*35m	m	130*86*43mm	130*86	6*66.5mm	160*86*43mm	
OTHERS		L*W*H	5"*3"*1.37"in	ch	5.11"*3.39"*1.69"inch	5.11"*3	3.39"*2.62"inch	6.3"*3.39"*1.69"inch	
	DACKING	P.W.	0.39Kg		0.51Kg 0.58Kg		g	0.64Kg	
		Q'TY	36pcs		24pcs 24pcs		S	24pcs	
	PACKING	G.W.	15Kg		13.2Kg	14.9K	g	16.4Kg	
		M'MENT	1.03CUFT		0.77CUFT	3 1		0.91CUFT	

- 1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25 of ambient temperature.
- 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1 µf & 47 µf parallel capacitor.
- 3. Tolerance: includes set up tolerance, line regulation and load regulation.
- 4. Derating may be needed under low input voltages. Please check the derating curve for more details.
- 5. Touch current was measured from primary input to DC output.


NOTE

- 6. The ambient temperature derating of 3.5°C/1000m with fanless models and of 5°C/1000m with fan models for operating altitude higher than 2000m(6500ft).
- 7. The power supply is considered a component which will be installed into a final equipment. All the Class I (with FG) EMC tests are executed by mounting the unit on a 360mm*360mm metal plate with 1mm of thickness. The Class II (without FG) EMC tests are executed by mounting the unit on a 130mm*86.6mm metal plate with 1mm of thickness. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com)




■ Block Diagram

PFC fosc: 90KHz PWM fosc: 100KHz



■ Output Derating vs Input Voltage





-30

0

10

20


30

AMBIENT TEMPERATURE ($^{\circ}\mathbb{C}$)

40

50

60



70 (HORIZONTAL)

0 10

20

30

AMBIENT TEMPERATURE ($^{\circ}$ C)

40

60

70 (HORIZONTAL)


Order No.	RPS-400	RPS-400-C	RPS-400-TF	RPS-400-SF
Products				A C
Convection	250W	250W		
Force Air	400W	400W	400W	400W




■ Mechanical Specification RPS-400 (PCB Type) Top View 127 5.6 115.8 5.7 31 42 Ф- \oplus HS1 HS4 21 LV - V $\overset{\perp}{\top}$ HS3 HS2 64.8 \oplus CN1 Air flow direction 5cm $\overset{\mathsf{FAN}}{\bowtie}$ 25CFM 3 0 max 35

Side View

















※ Mounting Instruction for -C/-TF/-SF Type

Hole No.	Recommended Screw Size	MAX. Penetration Depth L	Recommended mounting torque
1	M3	2mm	4~6Kgf-cm
2	M3	4mm	4~6Kgf-cm

Mounting Surface Chassis of RPS-400-C/TF/SF



※ CONNECTION

AC Input Connector (CN1): JST B3P-VH or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1	AC/N	JST VHR or equivalent	
2	No Pin		JST SVH-21T-P1.1 or equivalent
3	AC/L		or equivalent

DC Output Connector (CN2, CN3)

Pin No.	Assignment	Output Terminals
CN2	-V	M3.5 Pan HD screw in 2 positions
CN3	+V	Torque to 8 lbs-in(90cNm)max.

IN HS1,HS2,HS3,HS4 can not be shorted

Function Connector(CN11): TKP DH2I-2X2 or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1	-S		
2	+S	TKP DH2 or equivalent	TKP
3	DC COM		or equivalent
4	PG		

Function Connector(CN95): TKP DH2L-2X2 or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1	5Vsb	TIAD DITO	TKP
2,4	DC COM	TKP DH2 or equivalent	or equivalent
3	PS-ON	or oquiraioni	0.044

FAN Connector(CN12): TKP 8812-2 or equivalent (Except for RPS-400-TF/SF)

Pin No.	Assignment	Mating Housing	Terminal
1	DC COM	TKP 2502	TKP 8811
2	+12V	or equivalent	or equivalent

- Note: 1. When the input voltage is 230VAC, the PCB type (Blank-Type) model delivers EMI Class B for both conducted emission and radiated emission for the power supply; When the input voltage is 110VAC, the PCB type (Blank Type) model delivers EMI Class B for conducted emission and Class A for radiated emission for the power supply. It delivers Class A for conducted emission and radiated emission, when configured into Class II (no FG) system.
 - 2. The enclosed type (-C/TF/SF type) models are not suitable for configuration within a Class II (without FG) system, but suggested within a Class II (with FG) system.
 - 3. Mounting Instruction for enclosed type.

■ Installation Manual

Please refer to: http://www.meanwell.com/manual.html