

**Productname :** SERVISOL SUPER 10  
**Ref.Nr.:** UDS000043\_3\_20180611 (EN)  
**Creationdate :** 11.06.18 Version : 2.2  
**Replaces:** UDS000043\_20180530

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**SERVISOL SUPER 10**  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Precision

### 1.3. Details of the supplier of the safety data sheet

**CRC Industries UK Ltd.**  
Wylds Road  
Castlefield Industrial Estate  
TA6 4DD Bridgwater Somerset  
United Kingdom  
Tel.: +44 1278 727200  
Fax.: +44 1278 425644  
E-mail : hse.uk@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66

### 1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No 1272/2008

**Physical:** Aerosols, category 1  
Extremely flammable aerosol.  
Pressurised container: May burst if heated.

Classification is based on test data.

**Health:** Not classified

Classification based on calculation method.

**Environment:** Hazardous to the aquatic environment, chronic category 2  
Toxic to aquatic life with long lasting effects.

Classification based on calculation method.




**Productname :** SERVISOL SUPER 10  
**Ref.Nr.:** UDS000043\_3\_20180611 (EN) **Creationdate :** 11.06.18 Version : 2.2  
**Replaces:** UDS000043\_20180530

## 2.2. Label elements

### Labelling according to Regulation (EC) No 1272/2008

#### Hazard pictogram(s):



<b>Signal word:</b>	Danger
<b>Hazard statement(s):</b>	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H411 : Toxic to aquatic life with long lasting effects.
<b>Precautionary statement(s):</b>	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.
<b>Supplemental Hazard information:</b>	Repeated exposure may cause skin dryness or cracking.

## 2.3. Other hazards

No information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	01-2119485926-20	68512-91-4	270-990-9	30-60	Press. Gas, Flam. Gas 1	H280,H220	K,G
Hydrocarbons, C10-C12, Isoalkanes, less than 2% aromatics	01-2119471991-29	-	(923-037-2)	30-60	Flam. Liq. 3, Asp. Tox. 1, Aquatic Chronic 2	H226,H304,H411	Q
<b>Explanation notes</b>							
G : exempted from the obligation to register in accordance with art.2(7)of REACH Regulation No 1907/2006							
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)							
Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.							

(\* Explanation phrases : see chapter 16)

## SECTION 4: First aid measures



**Productname :** SERVISOL SUPER 10  
**Ref.Nr.:** UDS000043\_3\_20180611 (EN)  
**Creationdate :** 11.06.18 Version : 2.2  
**Replaces:** UDS000043\_20180530

#### 4.1. Description of first aid measures

<b>Contact with eyes :</b>	If substance has got into eyes, immediately wash out with plenty of water If eye irritation persists: Get medical advice/attention.
<b>Contact with skin :</b>	Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
<b>Inhalation :</b>	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Ingestion :</b>	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

#### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	May cause irritation. Symptoms : redness and pain

#### 4.3. Indication of any immediate medical attention and special treatment needed

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

foam, carbon dioxide or dry agent  
Do not use water jet extinguishing media, due to the risk of spreading fire.

#### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

#### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures



3 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate,  
Bridgwater, Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.crcind.com

**Productname :** SERVISOL SUPER 10  
**Ref.Nr.:** UDS000043\_3\_20180611 (EN)      **Creationdate :** 11.06.18 Version : 2.2  
**Replaces:** UDS000043\_20180530

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.  
In case of insufficient ventilation, wear suitable respiratory equipment.

## 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

## 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

## 6.4. Reference to other sections

For further information see section 8

# SECTION 7: Handling and storage

## 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
In case of insufficient ventilation, wear suitable respiratory equipment.  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.

## 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep out of reach of children.

## 7.3. Specific end use(s)

Cleaners - Precision

# SECTION 8: Exposure controls/personal protection

## 8.1. Control parameters

Exposure limits :



<b>Productname :</b> SERVISOL SUPER 10	<b>Creationdate :</b> 11.06.18 Version : 2.2
<b>Ref.Nr.:</b> UDS000043_3_20180611 (EN)	<b>Replaces:</b> UDS000043_20180530

No information available

## 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. It is good practice to wear gloves and to provide adequate ventilation whenever using the product. In all cases handle and use the product in accordance with good industrial hygiene practices.
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
<b>hands and skin :</b>	Depending on amount and duration of use and the risk of contact with the product the gloves manufacturer can assist you in the selection of the right glove material and breakthrough time.
Recommended gloves:	Nitrile
<b>eyes :</b>	Wear safety eyewear according to EN 166.
<b>Environmental protection:</b>	Avoid release to the environment. Collect spillage.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

<b>Apperance : physical state :</b>	Propane/butane propelled liquid.
<b>colour :</b>	Colorless.
<b>odour :</b>	Solvent.
<b>pH :</b>	Not applicable.
<b>Boiling point/range :</b>	153 °C
<b>Flash point :</b>	41 °C
<b>Evaporation rate :</b>	Not available.
<b>Explosion limits : upper limit :</b>	9.4 %
<b>lower limit :</b>	0.6 %
<b>Vapour pressure :</b>	Not available.
<b>Relative density :</b>	0.748 g/cm <sup>3</sup> (@ 20°C).
<b>Solubility in water :</b>	Insoluble in water
<b>Auto-ignition :</b>	> 200 °C
<b>Viscosity :</b>	Not available.

### 9.2. Other information

<b>VOC = volatile organic compounds</b>	626 g/l
---	---------



**Productname :** SERVISOL SUPER 10  
**Ref.Nr.:** UDS000043\_3\_20180611 (EN)

**Creationdate :** 11.06.18 Version : 2.2  
**Replaces:** UDS000043\_20180530

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO2

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

<b>acute toxicity:</b>	based on available data the classification criteria are not met
<b>skin corrosion/irritation:</b>	based on available data the classification criteria are not met
<b>serious eye damage/irritation:</b>	based on available data the classification criteria are not met
<b>respiratory or skin sensitisation:</b>	based on available data the classification criteria are not met
<b>germ cell mutagenicity:</b>	based on available data the classification criteria are not met
<b>carcinogenicity:</b>	based on available data the classification criteria are not met
<b>toxicity for reproduction:</b>	based on available data the classification criteria are not met
<b>STOT-single exposure:</b>	based on available data the classification criteria are not met
<b>STOT repeated exposure:</b>	based on available data the classification criteria are not met
<b>aspiration hazard:</b>	based on available data the classification criteria are not met

#### Information on likely routes of exposure:

<b>Inhalation :</b>	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.



**Productname :** SERVISOL SUPER 10  
**Ref.Nr.:** UDS000043\_3\_20180611 (EN) **Creationdate :** 11.06.18 Version : 2.2  
**Replaces:** UDS000043\_20180530

**Skin contact :** Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis  
Repeated exposure may cause skin dryness or cracking.  
**Eye contact :** May cause irritation.

**Toxicological data :**

No information available

**SECTION 12: Ecological information****12.1. Toxicity**

Hazardous to the aquatic environment, chronic category 2  
Toxic to aquatic life with long lasting effects.

**Ecotoxicological data:**

No information available

**12.2. Persistence and degradability**

No information available

**12.3. Bioaccumulative potential**

No information available

**12.4. Mobility in soil**

Insoluble in water

**12.5. Results of PBT and vPvB assessment**

No information available

**12.6. Other adverse effects**

No information available

**SECTION 13: Disposal considerations****13.1. Waste treatment methods**

**Product :** This material and its container must be disposed of in a safe way.  
Do not discharge into drains or the environment, dispose to an authorised



**Productname :** SERVISOL SUPER 10  
**Ref.Nr.:** UDS000043\_3\_20180611 (EN)

**Creationdate :** 11.06.18 Version : 2.2  
**Replaces:** UDS000043\_20180530

**National regulations :** waste collection point.  
Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number

UN-number : 1950

### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS

### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

### 14.4. Packing group

Packing group: Not applicable.

### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Regulation (EC) No 1907/2006 (REACH)  
Regulation (EC) No 1272/2008 (CLP)





<b>Productname :</b>	SERVISOL SUPER 10	<b>Creationdate :</b>	11.06.18 Version : 2.2
<b>Ref.Nr.:</b>	UDS000043_3_20180611 (EN)	<b>Replaces:</b>	UDS000043_20180530

Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

## 15.2. Chemical safety assessment

No information available

## SECTION 16: Other information

\*Explanation hazard statements: H220 : Extremely flammable gas.  
H226 : Flammable liquid and vapour.  
H280 : Contains gas under pressure; may explode if heated.  
H304 : May be fatal if swallowed and enters airways.  
H411 : Toxic to aquatic life with long lasting effects.

acronyms and synonyms: TWA = time weight average  
STEL = short time exposure limit  
VOC = volatile organic compounds  
PBT = persistent bioaccumulative toxic  
vPvB = very persistent very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

