

760 Amps 600 Volts AC/DC

marathon® ——Special Products

Product Data Sheet

145X301

Replace "x" with 1, 2, or 3 for number of poles

Power Terminal Block

Wire Range

Line: (2) 500 kcmil - #4
Load: (2) 500 kcmil - #4

Electrical Ratings

- 760 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C requirements
- Short circuit current ratings (SCCR): See SCCR section below for specifications.
- CU7AL 75°C connector terminal rating with copper or aluminum wire
- Factory & Field Wiring

Agency Compliance

- UR UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA certifed to C22.2 No. 158, File No. LR19766 (Wire classes B & C only)
- CE compliant to IEC 60947-7-1

Material Information

- Insulator base:
 - Phenolic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 150°C (UL RTI)
- Connector: aluminum, tin plated
- Terminal set screws: aluminum, tin plated
- · Connector mounting screws: steel, zinc plated
- RoHS compliant

A Regal Brand





Termination Specifications

Line & LoadSide	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) 1	
	500 kcmil	42.4 N·m (375 lbf·in)	1	В, С	
	400 - 2	42.4 N·m (375 lbf·in)	1	B, C, G, H, I (DLO)	
	4	42.4 N·m (375 lbf·in)	1	В, С	

Aluminum wire range: 500 kcmil - #4 AWG

Wire strip length: 1 3/8in. (35mm)Terminal screw drive: 3/8 in. hex

Short Circuit Current Ratings (SCCR)

- The suitable conductor ranges are limited to the table values only for achieving the SCCR in excess of the default rating of 10,000A.
- Other conductor combinations within the "Terminal Specifications" noted are suitable for achieving a SCCR of 10,000A (the default rating of terminal blocks).
- Enclosure size Investigated with a minimum 16x12x6 enclosure. Use in smaller enclosures is subject to end use evaluation.

SCCR With Fuses

Wire Class	1	able uctors	Max Overcurrent Protection Fuse Required Amp Rating / Class					SCCR RMS Sym. Amps	
	Line	Load	J	Т	RK1	RK5	G	CC	600V. Max
В, С	500 - 4	500 - 4	500	500	400	200	60	30	100,000
G, H, I	350 - 2	350 - 2	500	500	400	200	60	30	100,000
(*)	500 - 4	500 - 4	None						10,000

^{*} Any wire class evaluated (see terminal specification section)

¹ For information on copper stranded wire classes please visit: http://www.marathonsp.com/flexible-stranded-wire.php



Installation & Accessories

- Mounting (Panel):
 - For use with 1/4 fastener.
 - Torque mounting fastener to 30-40 lbf-in (3.4 4.5 N·m).
- Covers:
 - Flat covers available upon request
 - Catalog Number: CC 145x (replace "x" with number of poles)
 - Covers are clear polycarbonate
 - Accessory covers are not intended to provide insulation for electrical spacings.
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications.

Drawing

