

**KEMET Part Number: C1210C104K5HACTU**  
(C1210C104K5HAC7800)

SMD Comm X8R HT150C, Ceramic, 0.1 uF, 10%, 50 VDC, X8R, SMD, MLCC, High Temperature, Ultra-Stable, 1210



Dimensions	
<b>L</b>	3.2mm +/-0.2mm
<b>W</b>	2.5mm +/-0.2mm
<b>T</b>	1.25mm +/-0.15mm
<b>B</b>	0.5mm +/-0.25mm

Packaging Specifications	
<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	2500

General Information	
<b>Supplier:</b>	KEMET
<b>Series:</b>	SMD Comm X8R HT150C
<b>Style:</b>	SMD Chip
<b>Description:</b>	SMD, MLCC, High Temperature, Ultra-Stable
<b>Features:</b>	High Temperature, Ultra-Stable
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Marking:</b>	No
<b>Miscellaneous:</b>	Note: Referee time for X8R dielectric for this part number is 1000 hours
<b>Chip Size:</b>	1210

Specifications	
<b>Capacitance:</b>	0.1 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	50 VDC
<b>Dielectric Withstanding Voltage:</b>	125 V
<b>Temperature Range:</b>	-55/+150C
<b>Temperature Coefficient:</b>	X8R
<b>Dissipation Factor:</b>	2.50% 1kHz 25C
<b>Aging Rate:</b>	0% Loss/Decade Hour
<b>Insulation Resistance:</b>	10 GOhms