



[PRODUCT OVERVIEW](#) [VELLEMAN KITS & OSCILLOSCOPES](#) [INSTRUMENTS](#) [PERSONAL SCOPE](#)

USB FUNCTION GENERATOR

PCGU01

New



The new PC USB miniature function generator is simple to use and has a frequency range of up to 1 MHz!

This nifty measuring instrument can generate sine, square and triangle waveforms, and it has a DAC resolution of 10 bits. To top things off, it has an output of 0.2 Vpp to 10 Vpp.

Download the dedicated Windows® software and control the various signals. Among other things, the software includes a handy automated wave sequence generator.

Features

- dedicated Windows® software to control the various signals (free download)
- software includes an automated wave sequence generator
- design enclosure
- test leads
- free software download
- USB cable

Specifications

- DAC resolutions: 10 bits
- frequency range: sine, triangle form 1 Hz to 1 MHz, square wave 1 Hz to 100 kHz
- frequency setting resolution: 0.04 Hz
- sweep function
- amplitude range: 200 mVpp to 10 Vpp @ 1 kHz // no load / 0 V offset
- amplitude range with offset: 200 mVpp to 7.5 Vpp @ 1 kHz // no load / -2.5 V to +2.5 V offset
- offset range : from 0 to -2.5 V or +2.5 V max. (resolution 0.5% of full scale)
- waveforms: sine, square and triangle
- typical sine wave distortion (THD): < 0.02% @ 1 kHz / 0 dB / 600 Ohm
- square wave rise/fall time: < 0.2 μ s
- output impedance: 50 Ohm
- note: PC USB ground is connected to GND output
- minimum system requirements:
 - Windows® XP, Vista, 7, 8, 10
 - mouse or touchpad
 - free USB port 1.1 or 2.0