


KEMET, AE, Piezo Actuators, Multilayer



| Dimensions | |
|------------|---------------|
| L | 100mm NOM |
| W | 3mm +/-0.1mm |
| W2 | 3.4mm MAX |
| H | 18mm +/-0.1mm |
| T | 2mm +/-0.1mm |
| T2 | 2.4mm MAX |

| Packaging Specifications | |
|--------------------------|------|
| Weight: | 1.4 |
| Packaging: | Bulk |
| Packaging Quantity: | 10 |

| General Information | |
|---------------------|--|
| Style: | Resin Coated |
| Description: | Resin Coated Type Multilayer Piezoelectric Actuators |
| Young's Modulus: | 4.4x10 ¹⁰ N/m ² |

| Specifications | |
|------------------------|-------------|
| Series: | AE |
| Displacement: | 19um +/-2um |
| Voltage DC: | 150 VDC |
| Capacitance: | 0.4 uF |
| Capacitance Tolerance: | 20% |
| Resonant Frequency: | 76 kHz |
| Tensile Strength: | 20 N |
| Generated Force: | 200 N |
| Stiffness: | 10.5 N/um |
| Insulation Resistance: | 50 MOhms |
| Temperature Range: | -25/+85C |