

# Han-Eco 16B-HBM-with SL-with cover



| Part number        | 19 43 016 0341                      |
|--------------------|-------------------------------------|
| Specification      | Han-Eco 16B-HBM-with SL-with cover  |
| HARTING eCatalogue | https://b2b.harting.com/19430160341 |

## Identification

| Category                                       | Hoods/Housings            |
|--|---------------------------|
| Series of hoods/housingsHan-Eco <sup>®</sup> B |                           |
| Type of hood/housing                           | Bulkhead mounted housings |
| Description of hood/<br>housing                | With thermo-plastic cover |

### Version

| Locking type | Single locking lever |
|--------------|----------------------|
| Size         | 16 B                 |

### Technical characteristics

| Limiting temperature                   | -40 +125 °C |
|--|-------------|
| Number of relockings                   | ≥500        |
| Degree of protection acc. to IEC 60529 | IP66        |

## Material properties

| Material (hood/housing)                                    | Polyamide<br>Fibre-glass reinforced |
|--|-------------------------------------|
| Colour (hood/housing)                                      | RAL 9005 (jet black)                |
| Material (seal)  | NBR                                 |
| Colour (seal)  | RAL 9005 (jet black)                |
| Material (locking)   | Polyamide<br>Fibre-glass reinforced |
| Colour (locking)   | RAL 9005 (jet black)                |
| Material flammability class acc. to UL 94                  | V-0                                 |
| Material flammability class acc. to UL 94 (locking levers) | V-0                                 |

# Specifications and approvals

| Charifications | IEC 61984                     |
|----------------|-------------------------------|
| Specifications | EN 45545-2 R22: HL1, HL2, HL3 |



# Specifications and approvals

| EN 45545-2 R23: HL1, HL2, HL3 |
|-------------------------------|
| EN 45545-2 R24: HL1, HL2, HL3 |

### Commercial data

| Packaging size                 | 1        |
|--------------------------------|----------|
| Country of origin              | Germany  |
| European customs tariff number | 85389099 |