

**KEMET Part Number: C1812C334JARACTU**  
(C1812C334JARAC7800)

SMD Comm X7R Tip-Ring, Ceramic, 0.33 uF, 5%, 250 VDC, X7R, SMD, MLCC, Temperature Stable, Tin Termination, 1812



**Dimensions**

Dimension	Value
L	4.5mm +/-0.3mm
W	3.2mm +/-0.3mm
T	1.55mm +/-0.10mm
B	0.6mm +/-0.35mm

**Packaging Specifications**

<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	1000

**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	SMD Comm X7R Tip-Ring
<b>Style:</b>	SMD Chip
<b>Description:</b>	SMD, MLCC, Temperature Stable, Tin Termination
<b>Features:</b>	Tin Termination
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Marking:</b>	No
<b>Miscellaneous:</b>	Note: Referee time for X7R dielectric for this part number is 1000 hours
<b>Chip Size:</b>	1812

**Specifications**

<b>Capacitance:</b>	0.33 uF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage DC:</b>	250 VDC
<b>Dielectric Withstanding Voltage:</b>	625 V
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	X7R
<b>Dissipation Factor:</b>	2.50% 1kHz 25C
<b>Aging Rate:</b>	3% Loss/Decade Hour
<b>Insulation Resistance:</b>	3.03 GOhms