
KEMET Part Number: C322C680J2G5TA



GoldMax 300 Comm C0G, Ceramic, 68 pF, 5%, 200 VDC, C0G, GoldMax, Commercial Standard, Lead Spacing = 5.08mm



Dimensions		
L	5.08mm MAX	
Н	6.6mm MAX	
Т	3.18mm MAX	
S	5.08mm +/-0.78mm	
LL	7mm MIN	

Packaging Specifications		
Packaging:	Bulk, Bag	
Packaging Quantity:	500	

0.51mm +0.1/-0.025mm

F

General Information		
Supplier:	KEMET	
Series:	GoldMax 300 Comm C0G	
Style:	Radial	
Description:	GoldMax, Commercial Standard	
RoHS:	Yes	
Termination:	Tin	
Failure Rate:	N/A	
Halogen Free:	Yes	

Specifications		
Capacitance:	68 pF	
Capacitance Tolerance:	5%	
Voltage DC:	200 VDC	
Dielectric Withstanding Voltage:	500 V	
Temperature Range:	-55/+125C	
Temperature Coefficient:	COG	
Dissipation Factor:	0.10% 25C	
Aging Rate:	0% Loss/Decade Hour	
Insulation Resistance:	100 GOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

