

KEMET Part Number: CDR03BX563AKZR-T&R
(C1808P563K5XRL7189)

SMD Mil PRF55681, Ceramic, Military/High Reliability, 0.056 uF, 10%, 50 VDC, BX, R (0.01%/1000 Hrs), 1808




Dimensions

Dimension	Value
L	4.57mm +/-0.38mm (0.18 in +/-0.015 in)
W	2.03mm +/-0.38mm (0.08 in +/-0.015 in)
T	1.295mm +/-0.735mm (0.051 in +/-0.029 in)
B	0.51mm +/-0.25mm (0.02 in +/-0.01 in)

Packaging Specifications

Packaging:	T&R, 178mm, Plastic Tape
Packaging Quantity:	2500

General Information

Supplier:	KEMET
Series:	SMD Mil PRF55681
Style:	SMD Chip
RoHS:	No
Prop 65:	 WARNING: Cancer and reproductive harm - www.p65warnings.ca.gov
REACH:	SVHC (Pb - CAS 7439-92-1)
Termination:	Lead (SnPb)
Failure Rate:	R (0.01%/1000 Hrs)
Testing and Reliability:	MIL-PRF-55681
Qualifications:	MIL-PRF-55681
Miscellaneous:	Termination Description: SolderPlate 70-30
Chip Size:	1808

Specifications

Capacitance:	0.056 uF
Capacitance Tolerance:	10%
Voltage DC:	50 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	BX