

KEMET Part Number: C1206C471KGRACTU
(C1206C471KGRAC7800)

SMD Comm X7R HV, Ceramic, 470 pF, 10%, 2000 VDC, X7R, SMD, MLCC, High Voltage, Temperature Stable, 1206



Dimensions

| | |
|----------|-----------------|
| L | 3.2mm +/-0.2mm |
| W | 1.6mm +/-0.2mm |
| T | 1.2mm +/-0.15mm |
| B | 0.5mm +/-0.25mm |

Packaging Specifications

| | |
|----------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 2500 |

General Information

| | |
|-----------------------|--|
| Supplier: | KEMET |
| Series: | SMD Comm X7R HV |
| Style: | SMD Chip |
| Description: | SMD, MLCC, High Voltage, Temperature Stable |
| Features: | High Voltage |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Miscellaneous: | Note: Referee time for X7R dielectric for this part number is 1000 hours |
| Chip Size: | 1206 |

Specifications

| | |
|---|---------------------|
| Capacitance: | 470 pF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 2000 VDC |
| Dielectric Withstanding Voltage: | 2,400 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | X7R |
| Dissipation Factor: | 2.50% 1kHz 25C |
| Aging Rate: | 3% Loss/Decade Hour |
| Insulation Resistance: | 100 GOhms |