

KEMET Part Number: C0805C390KDGACTU
(C0805C390KDGAC7800)

SMD Comm C0G HV, Ceramic, 39 pF, 10%, 1000 VDC, C0G, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 0805



General Information

| | |
|---------------------|--|
| Supplier: | KEMET |
| Series: | SMD Comm C0G HV |
| Style: | SMD Chip |
| Description: | SMD, MLCC, Ultra-Stable, Low Loss, Class I |
| Features: | Ultra-Stable, Low Loss, Class I |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Chip Size: | 0805 |

Dimensions

| | |
|----------|------------------|
| L | 2mm +/-0.2mm |
| W | 1.25mm +/-0.2mm |
| T | 1.25mm +/-0.15mm |
| S | 0.75mm MIN |
| B | 0.5mm +/-0.25mm |

Specifications

| | |
|---|---------------------|
| Capacitance: | 39 pF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 1000 VDC |
| Dielectric Withstanding Voltage: | 1,200 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | C0G |
| Dissipation Factor: | 0.10% 1MHz 25C |
| Aging Rate: | 0% Loss/Decade Hour |
| Insulation Resistance: | 100 GOhms |

Packaging Specifications

| | |
|----------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 2500 |