

Description

- High Density, high current/low voltage applications
- Foil technology that adds higher reliability factor over the traditional magnet wire used for higher frequency circuit designs
- Current range from 78.0 to 33.8 Amps
- Inductance range from 0.50uH to 6.52uH
- Ferrite core material



Applications

- Next generation microprocessors
- Energy storage applications
- DC-DC converters
- Computers

Environmental Data

- Storage temperature range: -40°C to +125°C
- Operating ambient temperature range: -40°C to +85°C
- Solder reflow temperature: +260°C max. for 10 seconds max.

Packaging





- Supplied in bulk packaging, 24 parts per tray

Part Number	Rated Inductance μH	OCL (1) nominal $\pm 20\% \mu\text{H}$	I _{rms} (2) Amperes (Typ.)	I _{sat} (3) Amperes (Typ.)	DCR (m Ω) max. @ 20°C	Volts (4) μSec (μS) (ref.)
HC3-R50-R	0.50	0.50	78.00	120	0.42	17.33
HC3-1R0-R	1.0	1.05	78.00	78	0.42	17.33
HC3-2R2-R	2.2	2.05	55.50	60	0.70	26.01
HC3-3R3-R	3.3	3.63	42.45	46	1.20	34.65
HC3-4R7-R	4.7	4.98	33.80	38	2.17	43.30
HC3-5R6-R	5.6	5.68	33.80	34.5	2.17	43.30
HC3-6R0-R	6.0	6.52	33.80	30.0	2.17	43.30

- 1) Test Parameters: 300kHz, 0.25 Vrms
- 2) DC current for approximately ΔT of 40°C without core loss
De-rating is necessary for AC currents. PCB layout, trace thickness and width, air flow and proximity of other heat generating components will affect temperature rise. It is recommended that the temperature of the part not exceed 125°C under worst case conditions verified in the end application.
- 3) Peak current for approximately 30% rolloff (@20°C)
- 4) Applied Volt-Time product (V- μS) across the inductor. This value represents the applied V- μS at 300kHz necessary to generate a core loss equal to 10% of the total losses for a 40°C temperature rise.

Part number definition:
 HC3-XXX-R
 HC3 = Product code and size
 XXX = Inductance value in uH.
 R = Decimal point. If no R is present, third character = # of zeros
 -R suffix indicates RoHS compliant


Mechanical Diagrams



wwllly = Date code R = Revision level


Part Number	Height max
HC3-R50-R	18.0
HC3-1R0-R	17.5
HC3-2R2-R	17.5
HC3-3R3-R	17.5
HC3-4R7-R	17.5
HC3-5R6-R	17.5
HC3-6R0-R	17.5

Inductance Characteristics



Core Loss

Irms DERATING WITH CORE LOSS for HC3
% Applied Volt-u Seconds



This bulletin is intended to present product design solutions and technical information that will help the end user with design applications. Cooper Electronic Technologies reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Cooper Electronic Technologies also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Life Support Policy: Cooper Electronic Technologies does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.