

KEMET Part Number: C1210X224J5JACTU
(C1210X224J5JAC7800)

SMD Comm U2J Flex, Ceramic, 0.22 uF, 5%, 50 VDC, U2J, SMD, MLCC, FT-CAP, Ultra-Stable, 1210



Dimensions

L	3.3mm +/-0.4mm
W	2.6mm +/-0.3mm
T	1.55mm +/-0.15mm
B	0.6mm +/-0.25mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	2000

General Information

Supplier:	KEMET
Series:	SMD Comm U2J Flex
Style:	SMD Chip
Description:	SMD, MLCC, FT-CAP, Ultra-Stable
Features:	FT-CAP, Ultra-Stable
RoHS:	Yes
Termination:	Flexible Termination
Marking:	No
Miscellaneous:	Note: Referee time for U2J dielectric for this part number is 1000 hours
Chip Size:	1210

Specifications

Capacitance:	0.22 uF
Capacitance Tolerance:	5%
Voltage DC:	50 VDC
Dielectric Withstanding Voltage:	125 V
Temperature Range:	-55/+125C
Temperature Coefficient:	U2J
Dissipation Factor:	0.10% 1kHz 25C
Aging Rate:	0.1% Loss/Decade Hour
Insulation Resistance:	4.545 GOhms