

KEMET Part Number: C1210C125K3PACTU
(C1210C125K3PAC7800)

SMD Comm X5R, Ceramic, 1.2 uF, 10%, 25 VDC, X5R, SMD, MLCC, Temperature Stable, Class II, 1210



Dimensions	
L	3.2mm +/-0.2mm
W	2.5mm +/-0.2mm
T	0.95mm +/-0.10mm
B	0.5mm +/-0.25mm

Packaging Specifications	
Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	4000

General Information	
Supplier:	KEMET
Series:	SMD Comm X5R
Style:	SMD Chip
Description:	SMD, MLCC, Temperature Stable, Class II
Features:	Temperature Stable, Class II
RoHS:	Yes
Termination:	Tin
Marking:	No
Miscellaneous:	Note: Referee time for X5R dielectric for this part number is 1000 hours
Chip Size:	1210

Specifications	
Capacitance:	1.2 uF
Capacitance Tolerance:	10%
Voltage DC:	25 VDC
Dielectric Withstanding Voltage:	62.5 V
Temperature Range:	-55/+85C
Temperature Coefficient:	X5R
Dissipation Factor:	5.00% 1kHz 25C
Aging Rate:	5% Loss/Decade Hour
Insulation Resistance:	83 MOhms