

**KEMET Part Number: C1808W683KDRACTU**  
(C1808W683KDRAC7800)

ArcShield SMD Comm X7R HV, Ceramic, Anti-Arcing, 0.068 uF, 10%, 1000 VDC, X7R, SMD, MLCC, Arcshield, High Voltage, 1808



Dimensions	
<b>L</b>	4.7mm +/-0.5mm
<b>W</b>	2mm +/-0.2mm
<b>T</b>	2mm +/-0.15mm
<b>B</b>	0.7mm +/-0.35mm

Packaging Specifications	
<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	1000

General Information	
<b>Supplier:</b>	KEMET
<b>Series:</b>	ArcShield SMD Comm X7R HV
<b>Style:</b>	SMD Chip
<b>Description:</b>	SMD, MLCC, Arcshield, High Voltage
<b>Features:</b>	High Voltage
<b>RoHS:</b>	Yes
<b>Termination:</b>	Flexible Termination
<b>Marking:</b>	No
<b>Miscellaneous:</b>	Note: Referee time for X7R dielectric for this part number is 1000 hours. X7R dielectric is not recommended for AC line filtering or pulse applications
<b>Chip Size:</b>	1808

Specifications	
<b>Capacitance:</b>	0.068 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	1000 VDC
<b>Dielectric Withstanding Voltage:</b>	1,200 V
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	X7R
<b>Dissipation Factor:</b>	2.50% 1kHz 25C
<b>Aging Rate:</b>	3% Loss/Decade Hour
<b>Insulation Resistance:</b>	1.471 GOhms