

KEMET Part Number: C1206C105M4VACTU
(C1206C105M4VAC7800)

SMD Comm Y5V, Ceramic, 1 uF, 20%, 16 VDC, Y5V, SMD, MLCC, General Purpose, Class III, 1206



Dimensions

Dimensions	
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
T	1.2mm +/-0.20mm
B	0.5mm +/-0.25mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	2500

General Information

Supplier:	KEMET
Series:	SMD Comm Y5V
Style:	SMD Chip
Description:	SMD, MLCC, General Purpose, Class III
Features:	Class III
RoHS:	Yes
Termination:	Tin
Marking:	No
Miscellaneous:	Note: Referee time for Y5V dielectric for this part number is 1000 hours
Chip Size:	1206

Specifications

Capacitance:	1 uF
Capacitance Tolerance:	20%
Voltage DC:	16 VDC
Dielectric Withstanding Voltage:	40 V
Temperature Range:	-30/+85C
Temperature Coefficient:	Y5V
Dissipation Factor:	7.00% 1kHz 25C
Aging Rate:	7% Loss/Decade Hour
Insulation Resistance:	100 MOhms