

KEMET Part Number: CDR06BX474AKZS-T&R
(C2225P474K5XSL7189)

SMD Mil PRF55681, Ceramic, Military/High Reliability, 0.47 uF, 10%, 50 VDC, BX, S (0.001%/1000 Hrs), 2225




Dimensions

L	5.72mm +/-0.51mm (0.225 in +/-0.02 in)
W	6.35mm +/-0.51mm (0.25 in +/-0.02 in)
T	1.27mm +/-0.76mm (0.05 in +/-0.03 in)
B	0.51mm +/-0.25mm (0.02 in +/-0.01 in)

Packaging Specifications

Packaging:	T&R, 178mm, Plastic Tape
Packaging Quantity:	1100

General Information

Supplier:	KEMET
Series:	SMD Mil PRF55681
Style:	SMD Chip
RoHS:	No
Prop 65:	 WARNING: Cancer and reproductive harm - www.p65warnings.ca.gov .
REACH:	SVHC (Pb - CAS 7439-92-1)
Termination:	Lead (SnPb)
Failure Rate:	S (0.001%/1000 Hrs)
Testing and Reliability:	MIL-PRF-55681
Qualifications:	MIL-PRF-55681
Miscellaneous:	Termination Description: SolderPlate 70-30
Chip Size:	2225

Specifications

Capacitance:	0.47 uF
Capacitance Tolerance:	10%
Voltage DC:	50 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	BX