

**KEMET Part Number: C2225W564KCRAC7800**  
(C2225W564KCRAC7800)

ArcShield SMD Comm X7R HV, Ceramic, Anti-Arcing, 0.56 uF, 10%, 500 VDC, X7R, SMD, MLCC, Arcshield, High Voltage, 2225



**Dimensions**

<b>L</b>	5.9mm +/-0.75mm
<b>W</b>	6.4mm +/-0.4mm
<b>T</b>	2.5mm +/-0.20mm
<b>B</b>	0.7mm +/-0.35mm

**Packaging Specifications**

<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	500

**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	ArcShield SMD Comm X7R HV
<b>Style:</b>	SMD Chip
<b>Description:</b>	SMD, MLCC, Arcshield, High Voltage
<b>Features:</b>	High Voltage
<b>RoHS:</b>	Yes
<b>Termination:</b>	Flexible Termination
<b>Marking:</b>	No
<b>Miscellaneous:</b>	Note: Referee time for X7R dielectric for this part number is 1000 hours. X7R dielectric is not recommended for AC line filtering or pulse applications
<b>Chip Size:</b>	2225

**Specifications**

<b>Capacitance:</b>	0.56 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	500 VDC
<b>Dielectric Withstanding Voltage:</b>	750 V
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	X7R
<b>Dissipation Factor:</b>	2.50% 1kHz 25C
<b>Aging Rate:</b>	3% Loss/Decade Hour
<b>Insulation Resistance:</b>	179 MOhms