


C900AH SFTY X1-400 Y1-400, Ceramic, Safety, 2200 pF, 20%, 400 VAC (X1), 400 VAC (Y1), Y5V, Lead Spacing = 10mm



| General Information | |
|---------------------|---------------------------|
| Supplier: | KEMET |
| Series: | C900AH SFTY X1-400 Y1-400 |
| Style: | Radial Disc |
| RoHS: | Yes |
| Termination: | Tin |
| Failure Rate: | N/A |
| Qualifications: | UL, ENEC, VDE, CSA, CAN |
| Halogen Free: | Yes |

| Dimensions | |
|------------|-----------------|
| D | 9mm MAX |
| T | 5.5mm MAX |
| S | 10mm +/-1mm |
| LL | 18mm +2/-0mm |
| F | 0.55mm +/-0.1mm |

| Specifications | |
|----------------------------------|----------------------------|
| Capacitance: | 2200 pF |
| Capacitance Tolerance: | 20% |
| Voltage AC: | 400 VAC (X1), 400 VAC (Y1) |
| Dielectric Withstanding Voltage: | 4,000 V |
| Temperature Range: | -25/+125C |
| Temperature Coefficient: | Y5V |
| Dissipation Factor: | 5% |
| Insulation Resistance: | 10 GOhms |
| Safety Class: | X1/Y1 |

| Packaging Specifications | |
|--------------------------|--|
| Packaging: | Ammo, H0 = 18mm, Component Pitch = 25.4mm +/-2mm |
| Packaging Quantity: | 1000 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.