

**KEMET Part Number: C1206J225K4RACTU**  
(C1206J225K4RAC7800)

SMD Comm X7R FO, Ceramic, Open Mode, 2.2 uF, 10%, 16 VDC, X7R, SMD, MLCC, Open Mode, Temperature Stable, 1206



| Dimensions |                 |
|------------|-----------------|
| L          | 3.3mm +/-0.4mm  |
| W          | 1.6mm +/-0.35mm |
| T          | 0.9mm +/-0.20mm |
| B          | 0.6mm +/-0.25mm |

| Packaging Specifications |                          |
|--------------------------|--------------------------|
| Packaging:               | T&R, 180mm, Plastic Tape |
| Packaging Quantity:      | 4000                     |

| General Information |  |
|---------------------|--|
| Supplier:           | KEMET  |
| Series:             | SMD Comm X7R FO  |
| Style:              | SMD Chip   |
| Description:        | SMD, MLCC, Open Mode, Temperature Stable                                 |
| Features:           | Open Mode, Temperature Stable  |
| RoHS:               | Yes  |
| Termination:        | Flexible Termination   |
| Marking:            | No   |
| Miscellaneous:      | Note: Referee time for X7R dielectric for this part number is 1000 hours |
| Chip Size:          | 1206   |

| Specifications                   |                     |
|----------------------------------|---------------------|
| Capacitance:                     | 2.2 uF              |
| Capacitance Tolerance:           | 10%                 |
| Voltage DC:                      | 16 VDC              |
| Dielectric Withstanding Voltage: | 40 V                |
| Temperature Range:               | -55/+125C           |
| Temperature Coefficient:         | X7R                 |
| Dissipation Factor:              | 3.50% 1kHz 25C      |
| Aging Rate:                      | 3% Loss/Decade Hour |
| Insulation Resistance:           | 227 MOhms           |