


KEMET Part Number: ALS31A103KE100
(A431LH103M100A)

ALS31, Aluminum Electrolytic, 85C, 10,000 uF, 20%, 100 VDC, -40/+85C



Dimensions	
D	51mm +/-1mm
L	82mm +/-2mm
T	5.5mm +/-0.5mm
S	22.2mm +/-0.5mm
DT	13mm +/-0.5mm
LT	86.5mm +/-1mm
TD	10mm MIN
V	13.7mm NOM
Z	10mm NOM

Packaging Specifications	
Weight:	220 g
Sleeving:	Yes
Packaging:	Bulk, Box

General Information	
Supplier:	KEMET
Series:	ALS31
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Sleeving. MS (MxH) = M12x16

Specifications	
Capacitance:	10,000 uF
Capacitance Tolerance:	20%
Voltage DC:	100 VDC, 115 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	18000 Hrs (Rated Voltage And Ripple Current At 85C), 36000 Hrs (Rated Voltage At 85C)
Resistance:	28 mOhms (100Hz 20C), 24 mOhms (10kHz 20C)
Ripple Current:	10.1 Amps (100Hz 85C), 10.5 Amps (10kHz 85C)
Leakage Current:	6000 uA (5min 20C)