


KEMET Part Number: ALS31A332NF400
(A431TM332M400A)

ALS31, Aluminum Electrolytic, 85C, 3,300 uF, 20%, 400 VDC, -40/+85C



Dimensions	
D	77mm +/-1mm
L	105mm +/-2mm
T	5.5mm +/-0.5mm
S	31.8mm +/-0.5mm
DT	13mm +/-0.5mm
LT	110.5mm +/-1mm
TD	10mm MIN
V	19mm NOM
Z	10mm NOM

Packaging Specifications	
Weight:	690 g
Slewing:	Yes
Packaging:	Bulk, Box

General Information	
Supplier:	KEMET
Series:	ALS31
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Slewing. MS (MxH) = M12x16

Specifications	
Capacitance:	3,300 uF
Capacitance Tolerance:	20%
Voltage DC:	400 VDC
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	20000 Hrs (Rated Voltage And Ripple Current At 85C), 40000 Hrs (Rated Voltage At 85C)
Resistance:	49 mOhms (100Hz 20C), 36 mOhms (10kHz 20C)
Ripple Current:	13.4 Amps (100Hz 85C), 21.3 Amps (10kHz 85C)
Leakage Current:	6000 uA (5min 20C)