

KEMET Part Number: C0402C109B5GACTU
(C0402C109B5GAC7867)

SMD Comm C0G, Ceramic, 1 pF, +/-0.1 pF, 50 VDC, C0G, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 0402



| Dimensions | |
|------------|-----------------|
| L | 1mm +/-0.05mm |
| W | 0.5mm +/-0.05mm |
| T | 0.5mm +/-0.05mm |
| S | 0.3mm MIN |
| B | 0.3mm +/-0.1mm |

| Packaging Specifications | |
|--------------------------|------------------------|
| Packaging: | T&R, 180mm, Paper Tape |
| Packaging Quantity: | 10000 |

| General Information | |
|---------------------|---|
| Supplier: | KEMET |
| Series: | SMD Comm C0G |
| Style: | SMD Chip |
| Description: | SMD, MLCC, Ultra-Stable, Low Loss, Class I |
| Features: | Ultra-Stable, Low Loss, Class I |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Miscellaneous: | Note: KEMET 50V rated parts may be operated at 63 Volts |
| Chip Size: | 0402 |

| Specifications | |
|----------------------------------|---------------------|
| Capacitance: | 1 pF |
| Capacitance Tolerance: | +/-0.1 pF |
| Voltage DC: | 50 VDC |
| Dielectric Withstanding Voltage: | 125 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | C0G |
| Dissipation Factor: | 0.10% 1MHz 25C |
| Aging Rate: | 0% Loss/Decade Hour |
| Insulation Resistance: | 100 GOhms |