


R75L, Film, Metallized Polypropylene, General Purpose, 0.022 μ F, 10%, 560 VDC, 85C, Lead Spacing = 10mm



Dimensions

L	13mm +0.3mm
H	9mm +0.1mm
T	4mm +0.2mm
S	10mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
-------------------	-----------

General Information

Supplier:	KEMET
Series:	R75L
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Pulse, Capacitive Power Supply
RoHS:	Yes
Lead:	Wire Leads

Specifications

Capacitance:	0.022 μ F
Capacitance Tolerance:	10%
Voltage AC:	250 VAC
Voltage DC:	560 VDC, 336 VDC (105C)
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	4% 1kHz, 6% 10kHz, 25% 100kHz
Insulation Resistance:	1360 GOhms
Max dV/dt:	1500 V/us
Inductance:	10 nH