

**KEMET Part Number: PHE450KR7470JR06L2**  
(F450RP475J400C)

PHE450/F450, Film, Double Metallized Polypropylene, General Purpose, 4.7 uF, 5%, 400 VDC, 85C, Lead Spacing = 37.5mm



General Information	
<b>Supplier:</b>	KEMET
<b>Series:</b>	PHE450/F450
<b>Dielectric:</b>	Double Metallized Polypropylene
<b>Style:</b>	Radial
<b>Features:</b>	Pulse
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Miscellaneous:</b>	The Rated Voltage Decreases 1.3%/C Between +85C And +105C. Rthha= 17 C/W (85C), 0.2 m/s

Dimensions	
<b>L</b>	41mm MAX
<b>H</b>	38mm MAX
<b>T</b>	21mm MAX
<b>S</b>	37.5mm +/-0.4mm
<b>LL</b>	6mm -1mm
<b>F</b>	1mm +/-0.05mm
<b>G</b>	0.5mm NOM

Specifications	
<b>Capacitance:</b>	4.7 uF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage AC:</b>	250 VAC
<b>Voltage DC:</b>	400 VDC (85C), 296 VDC (105C)
<b>Temperature Range:</b>	-55/+105C
<b>Rated Temperature:</b>	85C
<b>Dissipation Factor:</b>	0.03% 1kHz
<b>Insulation Resistance:</b>	6.383 GOhms
<b>Max dV/dt:</b>	300 V/us
<b>Inductance:</b>	6 nH

Packaging Specifications	
<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	84

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.