


KEMET Part Number: MDC10475K50A52P3TUBE
(F153AA475K050T, MDC100ZA7470KA52P3L3)

MDC, Film, Metallized Polyester, Dual-In-Line, 4.7 uF, 10%, 30 VAC, 50 VDC, 85C, 10mm



Dimensions	
L	11mm +/-0.2mm
W	12.2mm +/-0.2mm
T	6.05mm +/-0.2mm
S	10mm +/-0.2mm
F	0.5mm +/-0.05mm

Packaging Specifications	
Packaging:	Bulk, Tube
Packaging Quantity:	43

General Information	
Supplier:	KEMET
Series:	MDC
Dielectric:	Metallized Polyester
Style:	Dual-In-Line
RoHS:	Yes
Lead:	L Leads

Specifications	
Capacitance:	4.7 uF
Capacitance Tolerance:	10%
Voltage AC:	30 VAC
Voltage DC:	50 VDC
Temperature Range:	-55/+125C
Rated Temperature:	85C
Dissipation Factor:	0.80% 1kHz, 1.50% 10kHz
Insulation Resistance:	1.0638 GOhms
Inductance:	4 nH