


KEMET Part Number: M3253504E2A104KZMB
(C0805K104K5RML)

SMD MIL X7R PRF32535, Ceramic, Military/High Reliability, 0.1 uF, 10%, 50 VDC, X7R, SMD, Conformal, Military, Low ESR, MIL-PRF-32535, N/A, 0805



Dimensions	
L	2.01mm +/-0.25mm (0.079 in +/-0.01 in)
W	1.27mm +/-0.25mm (0.05 in +/-0.01 in)
T	1.52mm MAX (0.06 in MAX)
B	0.51mm +/-0.25mm (0.02 in +/-0.01 in)

Packaging Specifications	
Weight:	20 mg
Packaging:	Waffle
Packaging Quantity:	80

General Information	
Supplier:	KEMET
Series:	SMD MIL X7R PRF32535
Style:	SMD Chip
Description:	SMD, Conformal, Military, Low ESR, MIL-PRF-32535
RoHS:	No
Prop 65:	 WARNING: Cancer and reproductive harm - www.p65warnings.ca.gov .
REACH:	SVHC (Pb - CAS 7439-92-1)
Termination:	Solder Plated
Failure Rate:	N/A
Qualifications:	MIL-PRF-32535
Notes:	2mm Pitch T&R packaging option will double quantity. Only for 0603 Chip Size
Chip Size:	0805

Specifications	
Capacitance:	0.1 uF
Capacitance Tolerance:	10%
Voltage DC:	50 VDC
Dielectric Withstanding Voltage:	125 V
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.50% 1MHz 25C
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	10 GOhms