


C4BS, Film, Metallized Polypropylene, Power, 0.33 uF, 10%, 700 VAC, 2000 VDC, 70C, Lead Spacing = 33mm



Dimensions

L	41.5mm NOM
H	40mm NOM
T	20mm NOM
S	33mm NOM
S1	41mm NOM
P	56mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	52

General Information

Supplier:	KEMET
Series:	C4BS
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	IGBT Circuit
RoHS:	Yes
Lead:	Flat Tabs
Miscellaneous:	Kemet Style E Tabs

Specifications

Capacitance:	0.33 uF
Capacitance Tolerance:	10%
Voltage AC:	700 VAC
Voltage DC:	2000 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Max dV/dt:	1379 V/us
Resistance:	7.2 mOhms (100KHz)
Ripple Current:	17 Amps (100kHz 70C), 455 Amps (Peak)
Inductance:	41 nH