

C4AF, Film, Metallized Polypropylene, Power, 3.3 uF, 10%, 250 VAC, 500 VDC, 85C, Lead Spacing = 27.5mm



General Information	
Supplier:	KEMET
Series:	C4AF
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Harsh Environmental Conditions
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200:	Yes
Miscellaneous:	Rth = 29 C/W

Dimensions	
L	31.5mm +0.5mm
H	29mm +0.2mm
T	19mm +0.3mm
S	27.5mm +/-0.4mm
LL	6mm +0/-2mm
F	0.8mm +/-0.05mm

Specifications	
Capacitance:	3.3 uF
Capacitance Tolerance:	10%
Voltage AC:	250 VAC
Voltage DC:	500 VDC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.07% MAX
Max dV/dt:	38 V/us
Resistance:	9 mOhms
Ripple Current:	8.9 Amps Irms (MAX), 125 Amps Ipk
Inductance:	26 nH (ESL)

Packaging Specifications	
Packaging:	Bulk, Box
Packaging Quantity:	72