


KEMET Part Number: PME271M633KR30
(P276EJ334K275A)

PME271M/P276, Film, Metallized Paper, Safety, 0.33 uF, 10%, 275 VAC (X2), 630 VDC, 110C, Lead Spacing = 25.4mm



General Information	
Supplier:	KEMET
Series:	PME271M/P276
Dielectric:	Metallized Paper
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC, UL, cUL
Construction:	Molded
Miscellaneous:	SRF= 2.1 MHz

Dimensions	
L	30.5mm MAX
H	19mm MAX
T	12.1mm MAX
S	25.4mm +/-0.5mm
LL	30mm +5mm
F	1mm NOM

Specifications	
Capacitance:	0.33 uF
Capacitance Tolerance:	10%
Voltage AC:	275 VAC (X2)
Voltage DC:	630 VDC
Temperature Range:	-40/+110C
Rated Temperature:	110C
Dissipation Factor:	1.3% 1kHz
Insulation Resistance:	12.121 GOhms
Max dV/dt:	400 V/us
Safety Class:	X2

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	100