


R46_275, Film, Metallized Polypropylene, Safety, 3.3 uF, 10%, 275 VAC (X2), 560 VDC, 110C, Lead Spacing = 27.5mm



General Information

| | |
|-----------------|-------------------------------------|
| Supplier: | KEMET |
| Series: | R46_275 |
| Dielectric: | Metallized Polypropylene |
| Style: | Radial |
| Features: | EMI Safety |
| RoHS: | Yes |
| Lead: | Wire Leads |
| Qualifications: | ENEC, UL, cUL, CQC |
| Notes: | We Recommended To Use R46 @ 310 VAC |

Dimensions

| | |
|----|-----------------|
| L | 32mm +0.3mm |
| H | 33mm +0.1mm |
| T | 18mm +0.2mm |
| S | 27.5mm +/-0.4mm |
| LL | 25mm +2/-1mm |
| F | 0.8mm +/-0.05mm |

Packaging Specifications

| | |
|---------------------|------|
| Packaging: | Tray |
| Packaging Quantity: | 128 |

Specifications

| | |
|------------------------|--------------|
| Capacitance: | 3.3 uF |
| Capacitance Tolerance: | 10% |
| Voltage AC: | 275 VAC (X2) |
| Voltage DC: | 560 VDC |
| Temperature Range: | -40/+110C |
| Rated Temperature: | 110C |
| Dissipation Factor: | 0.10% 1kHz |
| Insulation Resistance: | 9.0909 GOhms |
| Max dV/dt: | 150 V/us |
| Safety Class: | X2 |