


KEMET Part Number: PEH200XO4220MU2
(A351QM222M385A)

PEH200, Aluminum Electrolytic, 85C, 2,200 uF, 20%, 385 VDC, -40/+85C



General Information

Supplier:	KEMET
Series:	PEH200
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Slewing. M5
Shelf Life:	156 Weeks

Dimensions

D	66.6mm +/-1mm
L	106mm +/-1mm
T	3.8mm NOM
S	28.5mm
F	15mm +/-0.5mm
DT	15mm NOM
G	13mm NOM
LT	113mm +/-1mm
Z	13mm NOM

Packaging Specifications

Weight:	415 g
Slewing:	Yes
Packaging:	Bulk, Bag
Packaging Quantity:	12

Specifications

Capacitance:	2,200 uF
Capacitance Tolerance:	20%
Voltage DC:	385 VDC
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	15000 Hrs (Rated Voltage And Ripple Current At 85C)
Resistance:	38 mOhms (100Hz 20C), 20 mOhms (100kHz 20C)
Ripple Current:	9.6 Amps (100Hz 85C), 36.7 Amps (10kHz 50C), 26.1 Amps (10kHz 40C)
Leakage Current:	6541 uA (5min 20C)
Inductance:	16 nH (ESL)