

KEMET Part Number: PMR205AB6250M200R30
(P405QM254M125AH201)

PMR205/P405, Film, Metallized Paper, Resistor/Capacitor, 0.25 uF, 20%, 250 VDC, 85C, Lead Spacing = 15.2mm



General Information	
Supplier:	KEMET
Series:	PMR205/P405
Dielectric:	Metallized Paper
Style:	Radial
Features:	RC Unit not approved
RoHS:	Yes
Lead:	Wire Leads
Construction:	Molded
Miscellaneous:	Resistor Tolerance: +/-30%. Resistor= 200 Ohms

Dimensions	
L	18.5mm MAX
H	13mm MAX
T	7.3mm MAX
S	15.2mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Specifications	
Capacitance:	0.25 uF
Capacitance Tolerance:	20%
Voltage AC:	125 VAC
Voltage DC:	250 VDC
Temperature Range:	-40/+85C
Rated Temperature:	85C
Insulation Resistance:	3 GOhms
Safety Class:	X2

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	400