

A759, Polymer Aluminum, 125C LowZ, 10 uF, 20%, 160 VDC, -55/+125C, Lead Spacing = 3.5mm



Dimensions	
D	8mm +/-0.5mm
L	12mm +/-1mm
S	3.5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	19mm MIN
F	0.6mm +/-0.5mm

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	500

General Information	
Supplier:	KEMET
Series:	A759
Dielectric:	Polymer Aluminum
Description:	Single Ended, Polymer Aluminum
RoHS:	Yes
Lead:	Wire Leads

Specifications	
Capacitance:	10 uF
Capacitance Tolerance:	20%
Voltage DC:	160 VDC, 184 VDC (Surge)
Temperature Range:	-55/+125C
Rated Temperature:	125C
Life:	2000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
Dissipation Factor:	12.00% 120Hz 20c
Resistance:	110 mOhms (100kHz 20C)
Ripple Current:	1350 mAmps (100kHz 105C), 550 mAmps (100kHz 125C)
Leakage Current:	240 uA (2min 20C)
Impedance Ratio at -25C:	1.25
Impedance Ratio at -55C:	1.25