


A759, Polymer Aluminum, 125C LowZ, 150 uF, 20%, 63 VDC, -55/+125C, Lead Spacing = 5mm



Dimensions	
D	10mm +/-0.5mm
L	16mm +/-2mm
S	5mm +/-0.5mm
H0	18.5mm +/-0.5mm
F	0.6mm +/-0.5mm

Packaging Specifications	
Packaging:	Ammo
Packaging Quantity:	500

General Information	
Supplier:	KEMET
Series:	A759
Dielectric:	Polymer Aluminum
Description:	Single Ended, Polymer Aluminum
RoHS:	Yes
Lead:	Wire Leads

Specifications	
Capacitance:	150 uF
Capacitance Tolerance:	20%
Voltage DC:	63 VDC, 72.45 VDC (Surge)
Temperature Range:	-55/+125C
Rated Temperature:	125C
Life:	2000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
Dissipation Factor:	12.00% 120Hz 20c
Resistance:	48 mOhms (100kHz 20C)
Ripple Current:	2610 mAmps (100kHz 105C), 1520 mAmps (100kHz 125C)
Leakage Current:	1417.5 uA (2min 20C)
Impedance Ratio at -25C:	1.25
Impedance Ratio at -55C:	1.25