Photoelectric Sensor Series



Bulgin's slim line photoelectric sensor range offers a high degree of mechanical and electrical stability. A cost effective and flexible sensing solution. Designed specifically for manufacturing automation and industrial automation sensing operations.



- Sealed to IP67
- Stainless Steel 316 shell
- Cabled versions with or without connector
- O 2M cable length
- <0.5ms response time</p>
- NPN & PNP output


- O Detection distance 1 40mm
- Q Light point diameter 5.0mm at 30mm
- O Power supply voltage 12 24 VDC
- Ambient humidity 35 85%
- Operating temperature -10 to 50°C
- O Small body, just 4.5mm thick

Automation Sensors Photoelectric Sensor Series





- O Diffuse Reflective IP67 Sensors
- Choice of M5 Connector Termination
- Stainless Steel 316 BodyUp to 40mm Sensing Range



Part no.	Operation Mode	Output Configuration	Sensing Distance	Connection Method
SLLP3002M5	Light on	NPN	2 - 30mm	M5
SLDP3002M5	Dark on	NPN	2 - 30mm	M5
SLLN3002M5	Light on	PNP	2 - 30mm	M5
SLDN3002M5	Dark on	PNP	2 - 30mm	M5
SLLP4002M5	Light on	NPN	2 - 40mm	M5
SLDP4002M5	Dark on	NPN	2 - 40mm	M5
SLLN4002M5	Light on	PNP	2 - 40mm	M5
SLDN4002M5	Dark on	PNP	2 - 40mm	M5
SLLP3002CL	Light on	NPN	2 - 30mm	Cable
SLDP3002CL	Dark on	NPN	2 - 30mm	Cable
SLLN3002CL	Light on	PNP	2 - 30mm	Cable
SLDN3002CL	Dark on	PNP	2 - 30mm	Cable
SLLP4002CL	Light on	NPN	2 - 40mm	Cable
SLDP4002CL	Dark on	NPN	2 - 40mm	Cable
SLLN4002CL	Light on	PNP	2 - 40mm	Cable
SLDN4002CL	Dark on	PNP	2 - 40mm	Cable


Specifications

Photoelectric Sensor Series



Electrical Mechanical:

8 No. Poles: Locking Mechanism: Screw coupling Sealing: IP67 Current Rating: 0.5A Contact Accomodation: Voltage Rating (ac/dc): 48V 8 Pole 26AWG x 4P + AEB Contact Resistance: $<5m\Omega$ Cable: 6.2mm Dia Insulation Resistance: >100MO Terminations: Operating Temp Range: -25°C to 85°C PCB / Solder / Cable Mechanical Operation: 500 mating cycles Largest diameter over



SL

L + Light On D = Dark On

P = NPN

N = PNP

02 = 2M

30 = upto 30mm

40 = upto 40mm

M5 = M5 connector

CL = Blunt cut wire

Indicator: · Out Red;

· Stable operation: Green;

· Transmitters power supply: Green

coupling ring:

20.0mm

· Detection: Red & Green

Power voltage: 12 V~24VDC (±10%)

Current consumption: 11 mA

Output Control (normal): NPN output type:

The NPN collector is open below 24VDC, below 50mA Residual voltage: below 10mA, 10~30mA below 1.5V

Below 10mA, when 30~50mA below 2.0V

Leakage current: when load resistance $3K\Omega$ below 0.3mA

when load resistance 1K Ω below 0.5mA when load resistance 0.2K Ω below 1.5mA

Maximum switching load current: 50 mA

Minimum sensing object: ø1 mm

Operating temperature: -10 to 50°C

Ambient humidity: 35-85%


Sealing: IP67


Colour:

Vibration resistance: 10-50Hz double amplitudes, X. Y. Z. each direction 2 hours

Shock resistance: 1000m/s², X. Y. Z. each direction 6 times

·NPN output





Range:

Operation Mode:

Output Configuration:

Sensing Distance:

Cable Length:

Termination:

Materials: Cable Connectors: Sensor:

Body: TPU Stainless Steel 316

Coupling Nut: Nickel Plated Brass -

Blue

Pin Contacts: Brass, Gold plating -

Socket Contacts: Phosphor Bronze, Gold plating O Rings & Gaskets: Viton -

RoHS: Compliant Compliant Buccaneer for Data 3

Blue