


ALS70, Aluminum Electrolytic, 85C, 130,000 uF, 20%, 100 VDC, -40/+85C



General Information	
Supplier:	KEMET
Series:	ALS70
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Slewing

Dimensions	
D	90mm +/-1mm
L	194mm +/-2mm
T	5.5mm +/-0.5mm
S	31.8mm +/-0.5mm
DT	13mm +/-0.5mm
LT	198mm +/-1mm
TD	10mm MIN
V	25mm NOM
Z	10mm NOM

Specifications	
Capacitance:	130,000 uF
Capacitance Tolerance:	20%
Voltage DC:	100 VDC, 115 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	20000 Hrs (Rated Voltage And Ripple Current At 85C), 40000 Hrs (Rated Voltage At 85C)
Resistance:	6 mOhms (100Hz 20C), 8 mOhms (10kHz 20C)
Ripple Current:	40 Amps (100Hz 85C), 42.2 Amps (10 kHz 85C)
Leakage Current:	6000 uA

Packaging Specifications	
Weight:	1.8 kg
Slewing:	Yes
Packaging:	Tray