

ALS70, Aluminum Electrolytic, 85C, 1,800 uF, 20%, 250 VDC, -40/+85C



Dimensions	
D	36mm +/-1mm
L	82mm +/-2mm
T	7.14mm +/-0.5mm
S	12.8mm +/-0.5mm
DT	8mm +/-0.5mm
LT	87.5mm +/-1mm
TD	10mm MIN
V	8mm NOM

Packaging Specifications	
Weight:	115 g
Sleeving:	Yes
Packaging:	Tray

General Information	
Supplier:	KEMET
Series:	ALS70
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Sleeving

Specifications	
Capacitance:	1,800 uF
Capacitance Tolerance:	20%
Voltage DC:	250 VDC, 288 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	11000 Hrs (Rated Voltage And Ripple Current At 85C), 22000 Hrs (Rated Voltage At 85C)
Resistance:	131 mOhms (100Hz 20C), 86 mOhms (10kHz 20C)
Ripple Current:	5.5 Amps (100Hz 85C), 10.1 Amps (10 kHz 85C)
Leakage Current:	2700 uA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.