

T499, Tantalum, MnO2 Tantalum, High Temperature, 33 uF, 10%, 6.3 VDC, SMD, MnO2, Molded, Hi-Temp, 175C, Auto, AEC-Q200, N/A, 3 Ohms, 3528, Height Max = 2.1mm



Dimensions

Footprint	3528
L	3.5mm +/-0.2mm
W	2.8mm +/-0.2mm
H	1.9mm +/-0.2mm
T	0.13mm REF
S	0.8mm +/-0.3mm
F	2.2mm +/-0.1mm
A	1.9mm MIN
B	0.4mm +/-0.15mm
E	2.2mm REF
G	1.8mm REF
P	0.5mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Packaging Specifications

Weight:	107.45 mg
Packaging:	T&R, 178mm
Packaging Quantity:	2000

General Information

Supplier:	KEMET
Series:	T499
Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Description:	SMD, MnO2, Molded, Hi-Temp, 175C, Auto, AEC-Q200
Features:	Automotive, 175C
RoHS:	Yes
Termination:	Tin
Qualifications:	AEC-Q200
AEC-Q200:	Yes
Shelf Life:	156 Weeks
MSL:	1

Specifications

Capacitance:	33 uF
Capacitance Tolerance:	10%
Voltage DC:	6.3 VDC (85C), 4.9 VDC (125C), 2.1 VDC (175C)
Temperature Range:	-55/+175C
Rated Temperature:	85C
Dissipation Factor:	6.00% 120Hz 20C
Failure Rate:	N/A
Resistance:	3000 mOhms (100kHz)
Ripple Current:	168 mAmps (100kHz 25C), 151.2 mAmps (85C), 33.6 mAmps (175C)
Leakage Current:	2.1 uA (5min 20C)