


ALS71, Aluminum Electrolytic, 85C, 180,000 uF, 20%, 40 VDC, -40/+85C



Dimensions	
D	66mm +/-1mm
L	105mm +/-2mm
T	5.5mm +/-0.5mm
S	28.5mm +/-0.5mm
DT	13mm +/-0.5mm
LT	110.5mm +/-1mm
TD	10mm MIN
V	15.8mm NOM
Z	10mm NOM

Packaging Specifications	
Weight:	505 g
Slewing:	Yes
Packaging:	Tray

General Information	
Supplier:	KEMET
Series:	ALS71
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Slewing. MS (MxH) = M12 x 16

Specifications	
Capacitance:	180,000 uF
Capacitance Tolerance:	20%
Voltage DC:	40 VDC, 46 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	19000 Hrs (Rated Voltage And Ripple Current At 85C), 38000 Hrs (Rated Voltage At 85C)
Resistance:	9 mOhms (100Hz 20C), 9 mOhms (10kHz 20C)
Ripple Current:	27.4 Amps (100Hz 85C), 29.2 Amps (10 kHz 85C)
Leakage Current:	6000 uA