

C4AE, Film, Metallized Polypropylene, DC Link, 8 uF, 5%, 700 VDC, 70C, Lead Spacing = 27.5mm



Dimensions

L	31.5mm +0.5mm
H	29mm +0.2mm
T	19mm +0.3mm
S	27.5mm +/-0.4mm
LL	6mm -2mm
F	0.8mm NOM
G	0.5mm NOM

Packaging Specifications

Packaging:	Bulk, Box
-------------------	-----------

General Information

Supplier:	KEMET
Series:	C4AE
Dielectric:	Metallized Polypropylene
Style:	Radial
RoHS:	Yes
Termination:	Tin
Lead:	Wire Leads
Miscellaneous:	Thermal Resistance = 29 C/W

Specifications

Capacitance:	8 uF
Capacitance Tolerance:	5%
Voltage DC:	700 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Max dV/dt:	19 V/us
Resistance:	7.3 mOhms (10kHz 70C)
Ripple Current:	8 Amps (10kHz 70C), 154 Amps (Peak)
Inductance:	26 nH